

PRPG-43 | Replacement Part

By Powerohm Resistors
Catalog # [PRPG-43](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 32.89 Ohms,
10 A, MFG Part Number-PG-43

Features

Post Glover Replacement PartNumber-PG-43

General

Catalog Number	PRPG-43
Maximum Temperature Rise	375 °C
Resistance Ohms	32.89 Ohm
Type	Grid Resistor Type T2 & H3

Dimensions

Length26.5 in

Electrical Ratings

Current / Amperage Rating	10 A
Maximum Current Rating Amps	10 Amps
Continuous	
Wattage	3289 W

Product Assets

[Specifications - PRPG43](#)