

PRPG-44 | Replacement Part

By Powerohm Resistors
Catalog # [PRPG-44](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 41.76 Ohms, 9 A, MFG Part Number-PG-44

Features

Post Glover Replacement PartNumber-PG-44

General

Maximum Temperature Rise	375 °C
Resistance Ohms	41.76 Ohm
Type	Grid Resistor Type T2 & H3

Dimensions

Length	26.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	9 A
Maximum Current Rating Amps	9 Amps
Continuous	
Wattage	3383 W

Product Assets