

PRRH260-G | Replacement Part

By Powerohm
Catalog # [PRRH260-G](#)

Post Glover Replacement Part, HC Ribbon Resistor, 0.115 Ohms, 260 A, MFG Part Number-RH260-G



Features

- Post Glover Replacement PartNumber-RH260-G

General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.115 Ohm
Type	HC Wide Strip Resistor Type

Dimensions

Length	26.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	260 A
Maximum Current Rating Amps Continuous	260 Amps
Wattage	7774 W