

PRSSG140 | Replacement Part

By Powerohm
Catalog # [PRSSG140](#)



IPC Replacement Part, SSG Grid Resistor, 0.34 Ohms, 140 A,
MFG Part Number-SSG140

Features

- IPC MFG Part Number-SSG140

General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.34 Ohm
Type	Grid Resistor Type SSG

Dimensions

Length	26.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	140 A
Maximum Current Rating	140 Amps
Amps Continuous	