

## PRSSG84 | Replacement Part

By Powerohm  
Catalog # [PRSSG84](#)



IPC Replacement Part, SSG Grid Resistor, 1.09 Ohms, 84 A,  
MFG Part Number-SSG84

### Features

- IPC MFG Part Number-SSG84

### General

Maximum Temperature Rise	375 °C
Resistance Ohms	1.09 Ohm
Type	Grid Resistor Type SSG

### Dimensions

Length	26.5 in
--------	---------

### Electrical Ratings

Current / Amperage Rating	84 A
Maximum Current Rating	84 Amps
Amps Continuous	