

PRSW2-24 | Replacement Part

By Powerohm Resistors
Catalog # [PRSW2-24](#)

Post Glover Replacement Part, SW Smoothwound, 78 Ohms, 1.7 A, MFG Part Number-SW2-24



Features

Post Glover Replacement PartNumber-SW2-24

General

Application	Post Glover
Maximum Temperature Rise	375 °C
Resistance Ohms	78 Ohm
Type	Smoothwound Type SW

Dimensions

Length	6 in
--------	------

Electrical Ratings

Current / Amperage Rating	1.7 A
Maximum Current Rating Amps	1.7 Amps
Continuous	
Wattage	300 W

Product Assets