

## PRSW3-24 | Replacement Part

By Powerohm Resistors  
Catalog # [PRSW3-24](#)



Post Glover Replacement Part, SW Smoothwound, 136.1 Ohms,  
1.7 A, MFG Part Number-SW3-24

### Features

Post Glover Replacement PartNumber-SW3-24

### General

Application	Post Glover
Maximum Temperature Rise	375 °C
Resistance Ohms	136.1 Ohm
Type	Smoothwound Type SW

### Dimensions

Length	9 in
--------	------

### Electrical Ratings

Current / Amperage Rating	1.7 A
Maximum Current Rating Amps	1.7 Amps
Continuous	
Wattage	450 W

### Product Assets