

PRSW4-22 | Replacement Part

By Powerohm Resistors
Catalog # [PRSW4-22](#)



Post Glover Replacement Part, SW Smoothwound, 101 Ohms, 2.4 A, MFG Part Number-SW4-22

Features

Post Glover Replacement PartNumber-SW4-22

General

Application	Post Glover
Maximum Temperature Rise	375 °C
Resistance Ohms	101 Ohm
Type	Smoothwound Type SW

Dimensions

Length	12 in
--------	-------

Electrical Ratings

Current / Amperage Rating	2.4 A
Maximum Current Rating Amps	2.4 Amps
Continuous	
Wattage	600 W

Product Assets