

# Type R2 Dynamic Braking Resistor

By Powerohm Resistors  
Catalog # [R2-15A05](#)



Type R2 12.6 Ohms Braking Resistor For 230 V 15 H P 100%  
Braking Torque 50% Duty Variable Frequency Drives

## Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

## Application

Powerohm

## General

Braking Torque	100 %
Catalog Number	R2-15A05
Duty Cycling	50 %
Enclosure Type	GCE15
Horsepower - Maximum	15
Resistance Ohms	12.6 Ohm
System Voltage	230 V
Type	R2 Braking Resistor

## Product Assets

[Specifications - R2-15A05](#)