

Type R2 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R2-15B02](#)



Type R2 8.4 Ohms Braking Resistor For 230 V 15 H P 150%
Braking Torque 20% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

| | |
|----------------------|---------------------|
| Braking Torque | 150 % |
| Catalog Number | R2-15B02 |
| Duty Cycling | 20 % |
| Enclosure Type | GCE12 |
| Horsepower - Maximum | 15 |
| Resistance Ohms | 8.4 Ohm |
| System Voltage | 230 V |
| Type | R2 Braking Resistor |

Product Assets

[Specifications - R2-15B02](#)