

R4-125A01 | Powerohm Braking Resistor

By Powerohm
Catalog # [R4-125A01](#)

460 V 125 H P 100% Braking Torque 10% Duty 6 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

Application

Powerohm

General

Available Options	Mill Galvanized
Braking Torque	150 %
Duty Cycling	10 %
Enclosure Style	NEMA 1
Enclosure Type	GCE18
Horsepower - Maximum	125
Resistance Ohms	6 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Dimensions

Depth	10 in
Length	26.375 in
Width	10 in