

R4-15B01 | Powerohm Braking Resistor

By Powerohm
Catalog # [R4-15B01](#)

460 V 15 H P 150% Braking Torque 10% Duty 34 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

Application

Powerohm

General

Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	10 %
Enclosure Style	NEMA 1
Enclosure Type	GCE4
Horsepower - Maximum	15
Nominal Current (A)	11185.5
Resistance Ohms	34 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Dimensions

Depth	5 in
Length	12.375 in
Width	13 in