

R4-1A10 | Powerohm Braking Resistor

By Powerohm
Catalog # [R4-1A10](#)

460 V 1 H P 100% Braking Torque 100% Duty 750 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

Application

Powerohm

General

Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	100 %
Enclosure Style	NEMA 1
Enclosure Type	GCE3
Horsepower - Maximum	1
Resistance Ohms	750 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Dimensions

Depth	5 in
Length	12.375 in
Width	16 in