

R4-25A10 | Powerohm Braking Resistor

By Powerohm
Catalog # [R4-25A10](#)

460 V 25 H P 100% Braking Torque 100% Duty 30 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

Application

Powerohm

General

Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	100 %
Enclosure Style	NEMA 1
Enclosure Type	ED2
Horsepower - Maximum	25
Nominal Current (A)	18642.5
Resistance Ohms	30 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Dimensions

Depth	18 in
Length	30 in
Width	18 in