

# R4-2B10 | Powerohm Braking Resistor

By Powerohm  
Catalog # [R4-2B10](#)

460 V 2 H P 150% Braking Torque 100% Duty 250 Ohms



## Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

## Application

Powerohm

## General

Available Options	Mill Galvanized
Braking Torque	150 %
Duty Cycling	100 %
Enclosure Style	NEMA 1
Enclosure Type	GCE8
Horsepower - Maximum	2
Resistance Ohms	250 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

## Dimensions

Depth	5 in
Length	19.375 in
Width	13 in