

## R4-40A03 | Powerohm Braking Resistor

By Powerohm  
Catalog # [R4-40A03](#)

460 V 40 H P 100% Braking Torque 30% Duty 19 Ohms



### Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

### Application

Powerohm

### General

Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	30 %
Enclosure Style	NEMA 1
Enclosure Type	GCE24
Horsepower - Maximum	40
Resistance Ohms	19 Ohm
System Voltage	460 V

### Dimensions

Depth	10 in
Length	26.375 in
Width	13 in