

## R4-60A10 | Powerohm Braking Resistor

By Powerohm  
Catalog # [R4-60A10](#)

460 V 60 H P 100% Braking Torque 100% Duty 12.6 Ohms



### Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

### Application

Powerohm

### General

Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	100 %
Enclosure Style	NEMA 1
Enclosure Type	ED4
Horsepower - Maximum	60
Nominal Current (A)	44742
Resistance Ohms	12.6 Ohm
System Voltage	460 V

### Dimensions

Depth	32 in
Length	30 in
Width	18 in