

R4-10A02 | Powerohm Braking Resistor

By Powerohm Resistors
Catalog # [R4-10A02](#)

460 V 10 H P 100% Braking Torque 20% Duty 75 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	20 %
Enclosure Style	NEMA 1
Enclosure Type	GCE5
Horsepower - Maximum	10
Nominal Current (A)	7457
Resistance Ohms	75 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Dimensions

Depth	5 in
Length	12.375 in
Width	16 in

Product Assets