

Type R4 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R4-125A10](#)



Type R4 6 OhmsBraking Resistor For 460 V 125 H P 100%
Braking Torque 100% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	100 %
Catalog Number	R4-125A10
Duty Cycling	100 %
Enclosure Type	ED8
Horsepower - Maximum	125
Resistance Ohms	6 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Product Assets

[Specifications - R4-125A10](#)