

# Type R4 Dynamic Braking Resistor

By Powerohm Resistors  
Catalog # [R4-125B02](#)



Type R4 4 OhmsBraking Resistor For 460 V 125 H P 150%  
Braking Torque 20% Duty Variable Frequency Drives

**Features**

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

**Application**

Powerohm

**General**

Braking Torque	150 %
Catalog Number	R4-125B02
Duty Cycling	20 %
Enclosure Type	ED3
Horsepower - Maximum	125
Resistance Ohms	4 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

**Product Assets**

[Specifications - R4-125B02](#)