

# Type R4 Dynamic Braking Resistor

By Powerohm Resistors  
Catalog # [R4-125B05](#)



Type R4 4 Ohms Braking Resistor For 460 V 125 H P 150%  
Braking Torque 50% Duty Variable Frequency Drives

## Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

## Application

Powerohm

## General

Braking Torque	150 %
Catalog Number	R4-125B05
Duty Cycling	50 %
Enclosure Type	(2)ED5
Horsepower - Maximum	125
Resistance Ohms	4 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

## Product Assets

- [Literature - Dynamic Braking Resistors](#)
- [Specifications - R4-125B05](#)