

R4-20A01 | Powerohm Braking Resistor

By Powerohm Resistors
Catalog # [R4-20A01](#)

460 V 20 H P 100% Braking Torque 10% Duty 38 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	10 %
Enclosure Style	NEMA 1
Enclosure Type	GCE4
Horsepower - Maximum	20
Resistance Ohms	38 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Dimensions

Depth	5 in
Length	12.375 in
Width	13 in

Product Assets