

# R4-250B02 | Powerohm Braking Resistor

By Powerohm Resistors  
Catalog # [R4-250B02](#)



460 V 250 H P 150% Braking Torque 20% Duty 2 Ohms

## Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

## General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	150 %
Duty Cycling	20 %
Enclosure Style	NEMA 1
Enclosure Type	ED6
Horsepower - Maximum	250
Nominal Current (A)	186425
Resistance Ohms	2 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

## Dimensions

Depth	48 in
Length	30 in
Width	18 in

## Product Assets