

R4-25A02 | Powerohm Braking Resistor

By Powerohm Resistors
Catalog # [R4-25A02](#)

460 V 25 H P 100% Braking Torque 20% Duty 30 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	150 %
Duty Cycling	20 %
Enclosure Style	NEMA 1
Enclosure Type	GCE12
Horsepower - Maximum	25
Nominal Current (A)	18642.5
Resistance Ohms	30 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Dimensions

Depth	5 in
Length	26.375 in
Width	13 in

Product Assets