

# R4-30B05 | Powerohm Braking Resistor

By Powerohm Resistors  
Catalog # [R4-30B05](#)

460 V 30 H P 150% Braking Torque 50% Duty 17 Ohms



## Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

## General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	150 %
Duty Cycling	50 %
Enclosure Style	NEMA 1
Enclosure Type	ED3
Horsepower - Maximum	30
Nominal Current (A)	22371
Resistance Ohms	17 Ohm
System Voltage	460 V

## Dimensions

Depth	24 in
Length	30 in
Width	18 in

## Product Assets