

R4-40B05 | Powerohm Braking Resistor

By Powerohm Resistors
Catalog # [R4-40B05](#)



460 V 40 H P 150% Braking Torque 50% Duty 12.6 Ohms

Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	150 %
Duty Cycling	50 %
Enclosure Style	NEMA 1
Enclosure Type	ED3
Horsepower - Maximum	40
Nominal Current (A)	29828
Resistance Ohms	12.6 Ohm
System Voltage	460 V

Dimensions

Depth	24 in
Length	30 in
Width	18 in

Product Assets