

# R4-60A10 | Powerohm Braking Resistor

By Powerohm Resistors  
Catalog # [R4-60A10](#)

460 V 60 H P 100% Braking Torque 100% Duty 12.6 Ohms



## Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

## General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	100 %
Enclosure Style	NEMA 1
Enclosure Type	ED4
Horsepower - Maximum	60
Nominal Current (A)	44742
Resistance Ohms	12.6 Ohm
System Voltage	460 V

## Dimensions

Depth	32 in
Length	30 in
Width	18 in

## Product Assets