

# Type R4 Dynamic Braking Resistor

By Powerohm Resistors  
Catalog # [R4-60B03](#)



Type R4 8.4 Ohms Braking Resistor For 460 V 60 H P 150%  
Braking Torque 30% Duty Variable Frequency Drives

## Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

## Application

Powerohm

## General

Braking Torque	150 %
Catalog Number	R4-60B03
Duty Cycling	30 %
Enclosure Type	ED3
Horsepower - Maximum	60
Resistance Ohms	8.4 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

## Product Assets

[Specifications - R4-60B03](#)