

R4-75A01 | Powerohm Braking Resistor

By Powerohm Resistors
Catalog # [R4-75A01](#)



460 V 75 H P 100% Braking Torque 10% Duty 10 Ohms

Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	10 %
Enclosure Style	NEMA 1
Enclosure Type	GCE9
Horsepower - Maximum	75
Resistance Ohms	10 Ohm

Dimensions

Depth	5 in
Length	26.375 in
Width	10 in

Product Assets