

R4-75A02 | Powerohm Braking Resistor

By Powerohm Resistors
Catalog # [R4-75A02](#)

460 V 75 H P 100% Braking Torque 20% Duty 10 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	20 %
Enclosure Style	NEMA 1
Enclosure Type	GCE30
Horsepower - Maximum	75
Nominal Current (A)	55927.5
Resistance Ohms	10 Ohm
System Voltage	460 V

Dimensions

Depth	10 in
Length	26.375 in
Width	16 in

Product Assets