

Type R4 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R4-75B02](#)



Type R4 6.7 Ohms Braking Resistor For 460 V 75 H P 150%
Braking Torque 20% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	150 %
Catalog Number	R4-75B02
Duty Cycling	20 %
Enclosure Type	ED2
Horsepower - Maximum	75
Resistance Ohms	6.7 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Product Assets

[Specifications - R4-75B02](#)