

## R5-40A10 | Powerohm Braking Resistor

By Powerohm  
Catalog # [R5-40A10](#)

575 V 40 H P 100% Braking Torque 100% Duty 29 Ohms



### Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

### Application

Powerohm

### General

Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	100 %
Enclosure Style	NEMA 1
Enclosure Type	ED3
Horsepower - Maximum	40
Nominal Current (A)	29840
Resistance Ohms	29 Ohm
System Voltage	575 V

### Dimensions

Depth	24 in
Length	30 in
Width	18 in