



# Type R5 Dynamic Braking Resistor

By Powerohm Resistors  
Catalog # [R5-20B10](#)



Type R5 39 OhmsBraking Resistor For 575 V 20 H P 150%  
Braking Torque 100% Duty Variable Frequency Drives

### Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

### Application

Powerohm

### General

Braking Torque	150 %
Catalog Number	R5-20B10
Duty Cycling	100 %
Enclosure Type	ED3
Horsepower - Maximum	20
Resistance Ohms	39 Ohm
System Voltage	575 V
Type	R5 Braking Resistor

### Product Assets

[Specifications - R5-20B10](#)