

Type R5 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R5-30A10](#)



Type R5 39 OhmsBraking Resistor For 575 V 30 H P 100%
Braking Torque 100% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	100 %
Catalog Number	R5-30A10
Duty Cycling	100 %
Enclosure Type	ED3
Horsepower - Maximum	30
Resistance Ohms	39 Ohm
System Voltage	575 V
Type	R5 Braking Resistor

Product Assets

[Specifications - R5-30A10](#)