

# Type RH Resistor

By Powerohm Resistors  
Catalog # [RH200](#)



Type RH Ribbon Resistor 0.209 Ohms 200 A

## Features

- Insulated for 1000V
- Can be used AC/DC application
- Standard tolerance +/-10%
- 26.5"WX13"D6"H
- 40 LBS EA

## General

Catalog Number	RH200
Nominal Current (A)	8360
Resistance Ohms	0.209 Ohm
Size	8
System Voltage	600 VAC
Type	Ribbon Resistor Type RH

## Dimensions

Depth	13 in
Length	26.5 in
Weight	37 lb
Width	11 in

## Electrical Ratings

Amperage Rating	200 A
Current / Amperage Rating	200 A
Maximum Current Rating Amps	200 Amps
Continuous	
Wattage	8360 W

## Product Assets

[Specifications - RH200](#)