

# Type RH Resistor

By Powerohm Resistors  
Catalog # [RH225-D](#)



Type RH Double Ribbon Resistor 0.355 Ohms 225 A

## Features

- Insulated for 1000V
- Can be used AC/DC application
- Standard tolerance +/-10%
- 26.5"WX21.5"DX6"H
- 80 LBS EA

## General

Catalog Number	RH225-D
Resistance Ohms	0.355 Ohm
System Voltage	600 VAC
Type	Ribbon Resistor Type RH

## Dimensions

Depth	21.5 in
Length	26.5 in
Weight	72 lb
Width	19.44 in

## Electrical Ratings

Amperage Rating	225 A
Current / Amperage Rating	225 A
Maximum Current Rating Amps	225 Amps
Continuous	
Wattage	15836 W

## Product Assets

[Specifications - RH225-D](#)