

RH260-T | Type RH Ribbon Resistor

By Powerohm
Catalog # [RH260-T](#)



Type RH Ribbon Resistor 0.399 Ohms 260 A

General

Resistance Ohms	0.399 Ohm
System Voltage	600 VAC
Type	Ribbon Resistor Type RH

Dimensions

Depth	29 in
Length	26.5 in
Weight	112 lb
Width	27.75 in

Electrical Ratings

Amperage Rating	260 A
Current / Amperage Rating	260 A
Maximum Current Rating Amps Continuous	260 Amps
Wattage	26940 W