

RH300-D | Type RH Ribbon Resistor

By Powerohm
Catalog # [RH300-D](#)



Type RH Ribbon Resistor 0.224 Ohms 300 A

General

Resistance Ohms 0.224 Ohm
Type Ribbon Resistor Type RH

Dimensions

Depth 6 in
Length 26.5 in
Weight 81 lb
Width 19.437 in

Electrical Ratings

Current / Amperage Rating 300 A
Maximum Current Rating 300 Amps
Amps Continuous
Wattage 20196 W