

RH300 | Type RH Ribbon Resistor

By Powerohm
Catalog # [RH300](#)



Type RH Ribbon Resistor 0.132 Ohms 300 A

General

Nominal Current (A)	11880
Resistance Ohms	0.132 Ohm
Size	8
System Voltage	600 VAC
Type	Ribbon Resistor Type RH

Dimensions

Depth	13 in
Length	26.5 in
Weight	43 lb
Width	11 in

Electrical Ratings

Amperage Rating	300 A
Current / Amperage Rating	300 A
Maximum Current Rating Amps Continuous	300 Amps
Wattage	11880 W

Product Assets