

Type RH Resistor

By Powerohm Resistors
Catalog # [RH400](#)



Type RH Ribbon Resistor 0.076 Ohms 400 A

Features

- Insulated for 1000V
- Can be used AC/DC application
- Standard tolerance +/-10%
- 26.5"WX13"D6"H
- 40 LBS EA

General

Catalog Number	RH400
Nominal Current (A)	12160
Resistance Ohms	0.076 Ohm
Size	7
System Voltage	600 VAC
Type	Ribbon Resistor Type RH

Dimensions

Depth	13 in
Length	26.5 in
Weight	46 lb
Width	11 in

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Maximum Current Rating Amps	400 Amps
Continuous	
Wattage	12160 W

Product Assets

[Specifications - RH400](#)