

RH400-D | Type RH Ribbon Resistor

By Powerohm Resistors
Catalog # [RH400-D](#)



Type RH Ribbon Resistor 0.129 Ohms 400 A

General

Resistance Ohms	0.129 Ohm
System Voltage	600 VAC
Type	Ribbon Resistor Type RH

Dimensions

Depth	21.5 in
Length	26.5 in
Weight	87 lb
Width	19.44 in

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Maximum Current Rating Amps	400 Amps
Continuous	
Wattage	20672 W

Product Assets