

## RH400-T | Type RH Ribbon Resistor

By Powerohm Resistors  
Catalog # [RH400-T](#)



Type RH Ribbon Resistor 0.185 Ohms 400 A

### General

Catalog Number	RH400-T
Material	Metal/Porcelain
Resistance Ohms	0.185 Ohm
System Voltage	600 VAC
Type	Ribbon Resistor Type RH

### Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Maximum Current Rating Amps	400 Amps
Continuous	
Wattage	29549 W

### Dimensions

Cubic Capacity	4611 cu.in
Depth	29 in
Height	6 in
Weight	128 lb
Width	26.5 in