

# Type RH Resistor

By Powerohm Resistors  
Catalog # [RH450-T](#)



Type RH Triple Ribbon Resistor 0.136 Ohms 450 A

## Features

- Insulated for 1000V
- Can be used AC/DC application
- Standard tolerance +/-10%
- 26.5"WX29"DX6"H
- 120 LBS EA

## General

Catalog Number	RH450-T
Resistance Ohms	0.136 Ohm
System Voltage	600 VAC
Type	Ribbon Resistor Type RH

## Dimensions

Depth	29 in
Length	26.5 in
Weight	131 lb
Width	27.75 in

## Electrical Ratings

Amperage Rating	450 A
Current / Amperage Rating	450 A
Maximum Current Rating Amps	450 Amps
Continuous	
Wattage	27556 W

## Product Assets

[Specifications - RH450-T](#)