

PowerWell™ 30

Quazite Underground Enclosure with:
GFCI (Ground Fault Circuit Interrupter)
120V@30A Waterproof Outlet
Direct Burial Splice Kit



Features

- Safe and accessible power
- All components UL listed
- Reliable in wet and dry conditions

Specifications / Listings

- **Polymer Concrete Enclosure (Quazite)**

Tier 22 Load Rating
UL listed to ANSI/SCTE 77

- **GFCI**

120VAC Rated Voltage
Up to 30 Amps Current
3 wire - Single Phase
-35° to 66°C Operating Temperature
Auto Power Up
NEMA 4X IP69K Enclosure
cULus Recognized
Modified for submersible application

- **Cable**

10 AWG 3/C Flexible Cord
300V
-50°C - 105°C
UL listed
Watertight

- **Waterproof Outlet**

Thermoplastic Elastomer Watertight
Industrial/Commercial Grade
IP69K rating
Listed to UL498
Certified to CSA C22.2 No. 42
Meets NEMA WD-1, WD-6 And ANSI Standards
UL Listed to 4, 4X, 12, 6, 6P

- **Splice Kit**

Sealed Wire Connection System
600V maximum
#14-#8 AWG
UL 486D listed



Available Sizes
13x24x18

