

OptiChannel  
Fiber Connector  
OM2, MM

# HUBBELL

## Features

- Terminate in less than 60 Seconds
- RoHS Compliant and Bulk Packed in Recyclable Cartons

## Ordering Information

Description	Color	Catalog Number	UPC Number
Fiber Connector, Pre-Polished, 50uM, 12 Pack	Black	FCST50M12	662620217468



## Listings

Telcordia GR-326-CORE  
TIA-568-C.3  
TIA-604-FOCIS

## Performance

Environmental	
Operating temperature	0 °C to 70 °C
Optical	
Insertion loss	0.5dB (0.35dB typical), 0.75dB max
Mating durability	500 cycles, 0.1dB change
Multimode return loss	35dB Typ, 22dB minimum
Singlemode return loss	55dB Typ, 40dB minimum

## Online Resources

Customer Sales Drawings  
eCatalog  
Sales Drawing