

OptiChannel
Fiber Connector
OM1, MM

HUBBELL

Features

- Terminate in less than 60 Seconds
- RoHS Compliant and Bulk Packed in Recyclable Cartons

Ordering Information

Description	Color	Catalog Number	UPC Number
Fiber Optic Connectors, ST, Enhanced, OM1 Fiber, Pre-Polished, 12 Pack	Beige	FCST62M12	662620217475



Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Performance

Environmental	
Operating temperature	0 °C to 70 °C
Optical	
Insertion loss	0.5dB (0.35dB typical), 0.75dB max
Mating durability	500 cycles, 0.1dB change
Multimode return loss	35dB Typ, 22dB minimum
Singlemode return loss	55dB Typ, 40dB minimum

Online Resources

Customer Sales Drawings
eCatalog
Sales Drawing