

Features

- Premium Quality and High Performance Design

Ordering Information

Adapter Type	Color	Number of Ports	UPC Number	Catalog Number
LC Duplex	Violet	12	662620605340	FSPLCDS12VI

Listings

TIA-568-C.3
TIA-604-FOCIS

Specifications

Application	Interconnect
Connectivity	Receptacle
Size	5.1" X 1.1"
Material	Ceramic Zirconium
Mounting Hardware	Snap-In
Type	12) LC Duplex
Repeatability	0.1 dB SM / 0.2 dB MM
Back Reflection	-25 dB SM / -55 dB MM
Service Life	500 matings
Temperature Rating	-40 °C to +85 °C



Performance

Insertion Loss Max	Insertion Loss Typical
0.30 dB	0.20 dB

Online Resources

Customer Sales Drawings
eCatalog
Sales Drawing