



Box, FRP, 12"x12"x12", Tier 8, Gaskets

By QUAZITE
Catalog # B10121212G

Quazite® FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass
QuaziteFRP	Yes
Type	Below Ground Boxes
UPC	662037175382

Dimensions

Dimensions	12 in x 12 in x 12 in
Height	12 in
Length	12 in
Weight	29.4 lb
Width	12 in

Product Assets

[Catalogs - Underground Enclosures](#)

[Sales Drawings - Quazite 12 X 12 X 12 Box W/ Gasket Standard Version](#)

[Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)

[Video - PenCell® Enclosures](#)

[Video - Hubbell Power Systems How to Install Large Enclosures](#)



A Hubbell brand