



Box, FRP, 30"x48"x24", Tier 8

By QUAZITE
Catalog # [B10304824A](#)

Quazite FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass
Type	Below Ground Boxes
UPC	662037158453
Weight Load Rating (Design/Test)	8,000/12,000 lb

Dimensions

Dimensions	48 in x 30 in x 24 in
Height	24 in
Length	48 in
Weight	162.75 lb
Width	30 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Sales Drawings - Quazite 30 X 48 X 24 Box Standard Version \(B10304824A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-B10304824A-SPEC-EN | REV 1/2024