



Box, FRP, 24"x36"x24", Tier 8, Gaskets

By QUAZITE
Catalog # B13243624G

Quazite® FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass
QuaziteFRP	Yes
Type	Below Ground Boxes

Dimensions

Dimensions	36 in x 24 in x 24 in
Height	24 in
Length	36 in
Weight	114.45 lb
Width	24 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)